

BC-IM4

BC3

GR 1-2

GR 3-4

GR 5-6

GR 7-8

PGM

40 45 50 dB

36 55 60 65 MIC

28 70

25

PAD

5 10 20 ±dB 20

LINE

P48

LINE

2 3 4

1 5 6

AUX1

PRE

2 3 4

1 5 6

AUX2

PRE

2 3 4

1 5 6

AUX3

PRE

2 3 4

1 5 6

AUX4

PRE

CH-OUT

C L PAN R

3

CUE

POST

2 3 4

1 5 6

LEVEL

CUT

70 100 200 300 600 Hz

HPF

FILT

10 5 0 THR

15 5 10 15 20 dB

25 30

ATT

AUTOGAIN ON

.5 1 20 dB

.3 1 3 5ms

REL

EXP

.3 1 2 3 4 5s

.5 1 2 3 4 5 8 20

RAT

LIM

GR dB

4 9 15

0 4 9 15

HI

EXP-ON

1.5 7 10 15 kHz

.7 15

f

DYN

4 9 15

0 4 9 15

MID2

EQ

.25 1 2 3 kHz

.1 2 3

.06 3 kHz

MID1

INS

4 9 15

0 4 9 15

LOW

PAN

PAN

START

PFL

CH-ON 24

PK

PS

FDR OPEN

