

BC-IS6

BC3

GR 1-2

GR 3-4

GR 5-6

GR 7-8

PGM

LINE 2

L  R

Ø

0 4 8 12 16 20 ±dB 20  
GAIN

0 1 2 3 4 5 6  
AUX1

PRE

0 1 2 3 4 5 6  
AUX2

PRE

0 1 2 3 4 5 6  
AUX3

PRE

0 1 2 3 4 5 6  
AUX4

PRE

C L PAN R  
3

CH-OUT

0 1 2 3 4 5  
CUE

N-MINUS

0 1 2 3 4 5 6  
LEVEL

POST

CUT

40 70 100 200 300 600  
HPF Hz

FILT

.2 .4 .6 .8 1 ST 1.2 1.4 1.6 1.8 2  
MNO OVER

BASE

C L R  
DIR

INP MS

BASE

0 4 9 15 ±dB 15  
HI

.3 .7 1.5 3 7 10 15 kHz  
MID2

.1 .25 .5 1 2 3 kHz  
MID1

0 4 9 15 ±dB 15  
LOW

EQ

C L R  
BAL

BAL

START

PFL

PK

CH-ON 24

PS

FDR OPEN

